

## SBCP-11HY3R3H

Aliases (UPIO11HY3R3H00)

KEMET, SBCP-11HY, Power, 3.3 uH, 20%, 5mm



Click [here](#) for the 3D model.

Dimensions	
D	12.5mm MAX
L	12mm MAX
S	5mm +/-0.5mm
LL	3.5mm +/-0.5mm
F	0.6mm NOM

Packaging Specifications	
Component Weight	3.3 g
Packaging	Ammo
Packaging Quantity	1600

General Information	
Series	SBCP-11HY
Style	Through-Hole
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Core	Ferrite
Notes	Contains 4 Reels of 400 pieces each. Do Not Expose To Direct Sunlight.

Specifications	
Inductance	3.3 uH
Inductance Tolerance	20%
Temperature Range	-20/+105°C
Shielded	No
Current	4.4 Amps
DC Resistance	0.02 Ohms