


SBCP-80HY680H

Aliases (UPI080HY680H00)

KEMET, SBCP-80HY, Power, 68 uH, 10%, 5mm



Click [here](#) for the 3D model.

Dimensions

D	9.5mm MAX
L	11mm MAX
S	5mm +/-0.5mm
LL	3.5mm +/-0.5mm
F	0.6mm NOM

Packaging Specifications

Component Weight	2.5 g
Packaging	Ammo
Packaging Quantity	2000

General Information

Series	SBCP-80HY
Style	Through-Hole
Description	Radial Leaded, Ferrite Power Inductors
Features	DC-DC Converters, Nickel-Zinc (NiZn) Ferrite Core
RoHS	Yes
Lead	Wire Leads
Core	Ferrite
Notes	Contains 4 Reels of 500 pieces each.

Specifications

Inductance	68 uH
Inductance Tolerance	10%
Temperature Range	-20/+105°C
Shielded	No
Current	1.7 Amps
DC Resistance	0.16 Ohms

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.