

## Thread swivel coupler

### Technical characteristics

**Technology:** "One push" safety system (avoids hose whip)

**Operating pressure:** 2 to 12 bar

**Flow rate at 6 bar:** 1 820 l/min ( $\Delta P = 0,6$  bar)

**ID Passage:** 7,4 mm

**Temperature:** -15°C to +70°C

**Construction:** Composite body

**Highlight:** Anti-static, Non scratch



360° rotation in 2 axes

| A<br>(mm) | B<br>(mm) | C<br>(mm) | BSPP female thread | Parts Numbers |
|-----------|-----------|-----------|--------------------|---------------|
| 176,3     | 32,25     | 128,6     | G 3/8              | ESI 071102SW  |

