


Polyurethane recoils with rigid and swiveling male fittings



Technical characteristics

Max operating pressure: 8 bar

Temperature: -15°C to +70°C

Construction: Polyurethane

Highlight: Non scratch

Equipped with: Teflon-coated coupler

Red

BSPT male thread	ID/OD (mm)	Coil Ø (mm)	Max length (m)	Min. length (m)	Parts Numbers
R 1/4	6.5 x 10	42	4	0.4	PUS 64R
R 1/4	6.5 x 10	52	6	0.63	PUS 66R