














Series	Han® ES module	Han® HV Single module	Han® HV module	Han® HV module
Number of contacts	5	2	2	2
Termination	Cage-clamp terminal 	Crimp terminal 	Crimp terminal 	Crimp terminal 
Rated current	16 A	16 A	16 A	40 A
Rated voltage	400 V	2500 V	2900 / 5000 V	2900 / 5000 V
Wire gauge	0.14 ... 2.5 mm ²	0.5 ... 4 mm ²	0.5 ... 4 mm ²	1.5 ... 10 mm ²
Male insert (M)	09 14 005 2616	09 14 002 3025	09 14 002 3021	09 14 002 3023
Female insert (F)	09 14 005 2716	09 14 002 3125	09 14 002 3121	09 14 002 3123

Series	Han DD® module	Han DD® Quick Lock module	Han DD® Quick Lock module	Han® DDD module
Number of contacts	12	12	12	17
Termination	Crimp terminal 	Quick Lock termination with silver plated contacts 	Quick Lock termination with gold plated contacts 	Crimp terminal 
Rated current	10 A	10 A	10 A	10 A
Rated voltage	250 V	250 V	250 V	160 V
Wire gauge	0.14 ... 2.5 mm ²	0.25 ... 1.5 mm ²	0.25 ... 1.5 mm ²	0.14 ... 2.5 mm ²
Male insert (M)	09 14 012 3001	09 14 012 2632	09 14 012 2634	09 14 017 3001
Female insert (F)	09 14 012 3101	09 14 012 2732	09 14 012 2734	09 14 017 3101

Series	Han® High Density module	Han® D-Sub module		
Number of contacts	25	9		
Termination	Crimp terminal 	Crimp terminal 		
Rated current	4 A	5 A		
Rated voltage	50 V	50 V		
Wire gauge	0.08 ... 0.52 mm ²	0.08 ... 0.52 mm ²		
Male insert (M)	09 14 025 3001	09 14 009 3001		
Female insert (F)	09 14 025 3101	09 14 009 3101		

Series	Han® USB module	Han® FireWire module	Han® RJ45 module	
Number of contacts	4	6	8	
Modules	USB 2.0 Plug terminal 	IEEE 1394 	Ethernet Cat. 6 	
Male insert (M)	09 14 001 4601	09 14 001 4611	09 14 001 4623	
Female insert (F)	09 14 001 4701	09 14 001 4711	09 14 001 4721	