



## **NADB15FF**

15 pole D-SUB feedthrough, female to female, D-shape nickel housing

### **Features & Benefits**

- Ideal for audio networking and integration of equipment into video systems
- Universally accepted standard D-shape housing

**Technical Information**

Product	
<b>Title</b>	NADB15FF
<b>Gender</b>	female - female

Electrical	
<b>Contact resistance</b>	30 mΩ
<b>Insulation resistance</b>	> 5 GΩ
<b>Number of electrical contacts</b>	15
<b>Rated current per contact</b>	3 A
<b>Rated voltage</b>	50 V ac
<b>Dielectric strength</b>	> 0.5 kVac

Mechanical	
<b>Panel thickness</b>	4 mm
<b>Wiresize</b>	
<b>Wiring</b>	Feedthrough
<b>Mounting direction</b>	Front mounting
<b>Chassis shape</b>	D

Material	
<b>Contact plating</b>	Au
<b>Contacts</b>	Brass (CuZn39Pb3)
<b>Insert</b>	Steel , tin plated, PBT
<b>Shell</b>	Zinc diecast (ZnAl4Cu1)
<b>Shell plating</b>	Nickel

Environmental	
<b>Flammability</b>	UL 94-V0
<b>Temperature range</b>	-25 °C to +85 °C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NADB15FF](#)