



PC card drilling dimensions(after plating)
(thickness 2.40±0.20mm)



LEAD FREE PART NUMBER

SHELL	A±0.38	B±0.12	C±0.10	D±0.25	E±0.07	PART NUMBER
09	30.81	24.99	16.96	16.21	10.96	D09S24B.GX00LF
15	39.14	33.32	25.18	24.54	19.18	D15S24B.GX00LF
25	53.03	47.04	39.12	38.25	33.12	D25S24B.GX00LF
37	69.32	63.50	55.68	54.71	49.68	D37S24B.GX00LF

Performance class: 4 --> 200 mating/un-mating
6 --> 500 mating/un-mating



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8646-0000

mat'l. code	ISO 1302	tolerance	projection	product family
---	ISO 406 ISO 1001	ISO 406 ISO 1001	MM	D-SUB
Ltr	ecm no	dr	date	ISO 1302
G	EX-21654	AB	2015-10-28	tolerance unless otherwise specified
H	EX-42817	ACJ	2021-10-18	angles
				linear
				linear
				scale 2:1
				dr
				engn
				chr
				dppd
Sheet	revision	H		
index	sheet	1		

product family: D-SUB
title: FEMALE DELTA-D STRAIGHT, SOLDER TYPE
dwg no: C01-8646-0126
sheet 1 of 1
size: A3
type: Product Customer Drawing