



ITEM	DESCRIPTION	MATERIAL	QTY	SIZE	PART DRAWN NO	WT(Kg)
1	HEADER	SPCC	1	-	JD-MH-085	-
2	GLASS	HARD	3	-	JD-MG-055	-
3	LEAD	KOVAR	3	-	JD-ML-094	-
4	GND LEAD	KOVAR	1	-	JD-ML-095	-
5	BRAZED	BAg-8	1	-	JD-MG-007-3	-

- NOTE**
1. Insulation level : AC 500V 1sec, Not electrified;
 2. Tightness : $\leq 1 \times 10^{-8}$ atm, cc/sec;
 3. Insulation Resistance : 10GΩ Voltage DC200V measured point Header and Lead
 4. Ag lead tension : ≥ 3.0 Kg;
 5. No bubble and crack on the glass.
 6. Cross section of lead must be flat.
 7. Finish : Ni-ELP 3-5μm + Au PLATING 0.03μm MIN.

Designed by	Checked by	Approved	Reference	Date	Scale	Sheet
		JD-B-114Au		2015.07	-	
			Project Title			
			T0-46 3P4L OUTER 13.5mm			
			Drawing No. GEC-T046-104			

Mark	Revision	Date	Drawn	Check	Appr	Note
Ⓒ						
Ⓑ						
Ⓐ						