



Crocodile clips

MA 2 VA



Product	MA 2 VA
description	Miniature alligator clip with high strength insulation and 2 mm socket connection. Jaws and spring in stainless steel. The flat part of the jaws (fine wire section) allows a secure contact to be made when clamping even the thinnest wires. Capable of clamping flat components (soldering eyes) and wires up to a maximum diameter of 4 mm.
operating instruction	BA210
article-no. / *colour	9303191xx 
drawing	
technical data	
connection	2 mm socket
rated voltage ⁽¹⁾	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O ⁽³⁾
rated current ⁽¹⁾ (consider derating curve)	6 A
material socket	stainless steel
housing material	PP
temperature range acc. To IEC61010 ⁽²⁾	-25 °C to 70 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	HB
clamping range	4 mm

2 mm system

⁽¹⁾ for normal environmental conditions 5°C to 40°C

⁽²⁾ contact the manufacturer for applications at deviating temperature ranges

⁽³⁾ without rated measurement category, for other circuits that are not directly connected to mains

stand: 21.06.2022