

TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.15
.XX	±0.10





THIS IS A C.A.D. GENERATED DRAWING
DO NOT MAKE MANUAL REVISIONS TO MASTER.




ISSUE NUMBER

ORIGINAL

1



PCB LAYOUT
LAYOUT TOLERANCE: ±0.05MM



SPECIFICATION:

CONTACT:	BRASS
PLATING:	GOLD FLASH PLATING ALL OVER
INSULATION:	PA46, COLOR BLACK
VOLTAGE RATING:	12V
CURRENT RATING:	2A MAX
INSULATION RESISTANCE:	100MEGA OHMS MIN
DIELECTRIC WITHSTAND VOLTAGE:	100V RMS AT 60HZ
CONTACT RESISTANCE:	30mOHM MAX. BEFORE TEST AND 60mOHM MAX. AFTER TEST
MECHANICAL LIFE:	30000 CYCLES MIN.
OPERATING TEMPERATURE RANGE:	-30°C~+85°C
SALT SPRAY TEST TIME:	48H



THIS SERIES FULLY CONFORMS TO
THE EUROPEAN UNION DIRECTIVES
2011/65/EU FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC
TORONTO, ONTARIO
CANADA

THESE DRAWINGS AND SPECIFICATIONS
ARE THE PROPERTY OF EDAC INC., AND
SHALL NOT BE REPRODUCED, OR COPIED
OR USED AS THE BASIS FOR THE
MANUFACTURE OR SALE OF APPARATUS
WITHOUT WRITTEN PERMISSION.

POGO CONNECTOR, 5 POS, MALE

ACAD REFERENCE NO.: 686-0042231-121

DRAWN: E.S DATE: JUL.17/2022

CHECKED: J.L. DATE: AUG.04/2022

SCALE: (IN C.A.D. 1:1) SHEET 1 OF 1

DRAWING NUMBER: 686-0042231-121 ISSUE

PART NUMBER: 686-0042231-121 1