

Pos	pcs.	TG part number	description	remarks
1	1	J01010F2255	TNC Straight Plug Crimp	crimp/crimp
2	1	J01010F2255	TNC Straight Plug Crimp	crimp/crimp
3	500 mm	L01000A0003	RG-58 PVC	50 Ohm
4	1	B00081A1272	strain relief black	25 mm
5	1	B00081A1272	strain relief black	25 mm
6	0		labeling left	
7	0		labeling middle	
8	0		labeling right	

Technical Data:

cable:

cable name: RG-58 PVC
 impedance: 50 Ohm
 total length: 500 mm
 cable tolerance according to DIN 47101: 485 mm ±5 mm
 cable cut length: 490 mm -10 mm

connector left:



connector name: TNC Straight Plug Crimp
 connector design: straight
 protection: strain relief black
 assembly construction code: A0205

connector right:

connector name: TNC Straight Plug Crimp
 connector design: straight
 protection: strain relief black
 assembly construction code: A0205

quality check program number: L03200A0001

For your information only! Coax Configurator is subject to technical verification!

2015	date	name			prod.order.no.	
	10.06.2015	autom.				
scale	title				 Telegärtner	
	RF - cable assembly					
dim. without tolerances according to	doc.type	ref.no.	L09999B3589 RoHS compliant			 dimensions: mm Original: DIN A4