



DATE	SYM	REVISION RECORD	AUTH	DR.	CK.
12/05/08	A	ADDED "ROHS COMPLIANT"	T.B.	B.S.	

ORDERING CODE BH510D

SOLDER LUGS = L
 (6") WIRE LEADS = W
 9VOLT TYPE SNAPS = SF



VIEW "AA"




SPECIFICATIONS:

WIRE LEADS SHOWN ABOVE

- Plastic material - polypropylene
- Flammability Rating-UL94 HB, UL File No. E216959
- Temperature Range: -10°C to +100°C
- Springs - nickel plated spring steel
- Wire - 152.4 mm Long 26 AWG, UL1007, CSA - TR-64, 300V, 80° C.
- Rivets - Brass, nickel plated
- 9 Volts Snaps - Brass, nickel plated
- Contact Resistance: Under 50mΩ for +/- contacts per EIA-540J000
- ROHS COMPLIANT

Note: Dimensions in mm. (inches)

TOLERANCES (EXCEPT AS NOTED)	 Memory Protection Devices, Inc. 200 Broad Hollow Road, Farmingdale, New York 11735		
DECIMAL + .5 (.020") - .5 (.020")	SCALE	DRAWN BY	S.C.
FRACTIONAL + .8 (.030") - .8 (.030")	APPROVED BY		
ANGULAR + 3° - 3°	DATE	DRAWING NUMBER	
	12/05/2008	BH510DW	
		TITLE	
		TEN "D" CELL HOLDER	