



Part Number : [191210029](#)


Product Description : InsulKrimp Flanged Spade Tongue Terminal for 14-16 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier

Series Number : 19121

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : BB-216-08XT



Documents & Resources

Drawings

[Drawing 191210029_sd.pdf](#)

3D Models and Design Files

[3D Model 191210029_stp.zip](#)

Specifications

[Product Specification PS-19902-009-001.pdf](#)

[Product Specification PS-19902-015-001.pdf](#)

[Product Specification PS-19902-011-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS

- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19121
Description	InsulKrimp Flanged Spade Tongue Terminal for 14-16 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier
Keyword	Spade Terminal, Spade Terminals
Product Family	Solderless Terminals
Product Name	InsulKrimp
Type	Spade
UPC	800753095632

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.734/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	4.064µm

Plating min - Termination	4.064µm
Stud Size	8 (M4)
Wire Insulation Diameter	4.45mm
Wire Size (AWG)	14, 16
Wire Size mm ²	1.00-2.50

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>0192880123</u>
Mini-Mac Applicator	<u>0638850400</u>

This document was generated on Dec 11, 2023