

Typical Application



QX-17A-N

- Medical Appliances
- Optical Instruments
- Communication Equipment
- Precios Apparatus and meter
- Other Industrial
- Toys and Models

Precious metal-brush motor


Output : Appro 0.1W ~ 0.8W

Model	Voltage		Free load		At Max. Efficiency				Stall Torque (g.cm)
	Operating range	Nominal Voltage (V)	Speed (r.p.m.)	Current (A)	Speed (r.p.m.)	Current (A)	Torque (g.cm)	Output (W)	
QX-17A-N-110100	2~5	4.5	5600	0.03	4480	0.12	7	0.33	35

Dimensions

Unit: mm


DIRECTION OF ROTATION



Weight: 23g (Approx)

Characteristic Curve

QX-17A-N-110100 4.5V



Electrical characteristic for reference only (w/ ±15% tolerance)