

Distribution terminal block; with operating slots;  $1 \times 6 \text{ mm}^2 / 6 \times 1.5 \text{ mm}^2$ ; with integrated end plate; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 6,00 mm²; red



https://www.wago.com/2006-8033





### Electrical data

Ratings per IEC/EN	
Nominal voltage (III/3)	800 V
Rated impulse voltage (III/3)	8 kV
Rated current	41 A
Rated current 2	57 A
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3

Connection data	
Total number of connection points	7
Total number of potentials	1
Number of levels	1
Number of jumper slots	2

Connection 1	
Connection type 1	Input
Connection technology	Push-in CAGE CLAMP®
Number of connection points	1
Actuation type	Push-in Operating tool
Connectable conductor materials	Copper
Nominal cross-section	6 mm²
Solid conductor	0.5 10 mm² / 20 8 AWG
Solid conductor; push-in termination	2.5 10 mm² / 14 8 AWG
Fine-stranded conductor	0.5 10 mm² / 20 8 AWG
Fine-stranded conductor; with insulated ferrule	0.5 6 mm² / 20 10 AWG
Fine-stranded conductor; with ferrule; push-in termination	2.5 6 mm² / 16 10 AWG
Note (conductor cross-section)	Depending on the conductor characteristic, a conductor with a smaller cross-section can also be inserted via push-in termination.
Strip length	13 15 mm / 0.51 0.59 inch
Wiring direction	Front-entry wiring

# Data sheet | Item number: 2006-8033 https://www.wago.com/2006-8033



Connection 2	
Connection type 2	Output
Connection technology 2	Push-in CAGE CLAMP®
Number of connection points 2	6
Nominal cross-section 2	1.5 mm <sup>2</sup>
Solid conductor 2	0.25 2.5 mm² / 22 14 AWG
Solid conductor; push-in termination 2	0.75 2.5 mm² / 18 14 AWG
Fine-stranded conductor 2	0.25 2.5 mm² / 22 14 AWG
Fine-stranded conductor; with insulated ferrule 2	0.25 1.5 mm² / 22 16 AWG
Fine-stranded conductor; with ferrule; push-in termination; 2	0.75 1.5 mm² / 18 16 AWG
Strip length 2	9 11 mm / 0.35 0.43 inch

Physical data	
Width	9 mm / 0.354 inch
Height	73.8 mm / 2.905 inch
Depth from upper-edge of DIN-rail	32.9 mm / 1.295 inch

Mechanical data	
Mounting type	DIN-35 rail
Marking level	Center/side marking

Material data	
Note (material data)	Information on material data can be found here
Color	red
Insulation material	Polyamide (PA66)
Flammability class per UL94	VO
Clamping spring material	Chrome-nickel spring steel (CrNi)
Fire load	0.316 MJ
Weight	16.3 g

Commercial data	
PU (SPU)	12 Pieces
Country of origin VKOrg Germany	DE
GTIN	4055144134872
Customs tariff number VKOrg Germany	85369010000

#### Downloads

### **Environmental Product Compliance**

Compliance Search Environmental Product Compliance 2006-8033



https://www.wago.com/2006-8033



#### Documentation

#### Additional Information

**Technical Section** 

pdf 2142.18 KB



#### CAD/CAE-Data

#### CAD data

2D/3D Models 2006-8033

 $\downarrow$ 

#### 1 Compatible products

#### 1.1 Optional accessories

#### 1.1.1 DIN-rail

### 1.1.1.1 Mounting accessories



#### Item no.: 210-196

Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored



#### Item no.: 210-118

Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715; silver-colored



Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715; copper-colored



### Item no.: 210-115

Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 18 mm; silver-colored

#### Item no.: 210-197

Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; similar to EN 60715; silver-colored



#### Item no.: 210-112

Steel carrier rail;  $35 \times 7.5$  mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 25 mm; silver-colored

### Item no.: 210-114

Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored



### )-112 <u>Item no.: 210-113</u>

Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; according to EN 60715; silver-colored

#### 1.1.2 Ferrule

#### 1.1.2.1 Ferrule



Ferrule; Sleeve for 0.75 mm² / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray

#### Item no.: 216-263

Ferrule; Sleeve for 1 mm² / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red

#### Item no.: 216-264

Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black

#### Item no.: 216-266

Ferrule; Sleeve for 2.5 mm<sup>2</sup> / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue



#### Item no.: 216-267

Ferrule; Sleeve for 4 mm² / AWG 12; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray

#### Item no.: 216-208

Ferrule; Sleeve for 6 mm² / AWG 10; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; yellow

https://www.wago.com/2006-8033



#### 1.1.3 Installation

#### 1.1.3.1 Mounting accessories



Item no.: 709-169

Cover carrier; Type 3; gray



Item no.: 709-156

Cover; Type 3; suitable for cover carrier, type 3; 1 m long; transparent

#### 1.1.4 Jumper

#### 1.1.4.1 Jumper







Item no.: 2001-402

Jumper; 2-way; insulated; light gray

Item no.: 2001-403

Jumper; 3-way; insulated; light gray

Item no.: 2001-404

Jumper; 4-way; insulated; light gray

#### 1.1.5 Marking

#### 1.1.5.1 Group marker carrier







Item no.: 2009-191

Group marker carrier; gray

Item no.: 2009-192 Group marker carrier; gray Item no.: 2009-193

Group marker carrier; gray

#### 1.1.5.2 Marker

#### Item no.: 2009-145/000-006

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue

#### Item no.: 2009-145/000-007

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray

#### Item no.: 2009-145/000-023

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green

#### Item no.: 2009-145/000-012

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange

#### Item no.: 2009-145/000-005

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; red

#### Item no.: 2009-145/000-024

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; violet

#### Item no.: 2009-145

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

#### Item no.: 2009-145/000-002

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; yellow



## Item no.: 248-501/000-006

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; blue

#### Item no.: 248-501/000-007

Item no.: 248-501/000-005

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; gray

#### Item no.: 248-501/000-023

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; green

#### Item no.: 248-501/000-017

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; light green



#### Item no.: 248-501/000-012

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; orange

Mini-WSB marking card; as card; not

stretchable; plain; snap-on type; red

### Item no.: 248-501/000-024

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; violet

#### Item no.: 248-501 Mini-WSB marking card; as card; not stret-

### Item no.: 248-501/000-002

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; yellow

#### Item no.: 793-5501/000-006

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; blue

#### Item no.: 793-5501/000-007

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; gray

## Item no.: 793-5501/000-023

chable; plain; snap-on type; white

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; green



### Item no.: 793-5501/000-017

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; light green

#### Item no.: 793-5501/000-012

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; orange

### Item no.: 793-5501/000-005

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; red

## Item no.: 793-5501/000-024

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; violet

https://www.wago.com/2006-8033



#### 1.1.5.2 Marker

Item no.: 793-5501







WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; white



Item no.: 793-501/000-006 WMB marking card; as card; not stretchable; plain; snap-on type; blue Item no.: 793-501/000-007 WMB marking card; as card; not stretchable; plain; snap-on type; gray



Item no.: 793-501/000-023

WMB marking card; as card; not stretchable; plain; snap-on type; green



WMB marking card; as card; not stretcha-

ble; plain; snap-on type; light green

Item no.: 793-501/000-012

WMB marking card; as card; not stretchable; plain; snap-on type; orange



Item no.: 793-501/000-005

WMB marking card; as card; not stretchable; plain; snap-on type; red



Item no.: 793-501/000-024

WMB marking card; as card; not stretchable; plain; snap-on type; violet



Item no.: 793-501/000-017

Item no.: 793-501 WMB marking card; as card; not stretchable; plain; snap-on type; white



WMB marking card; as card; not stretchable; plain; snap-on type; yellow

Item no.: 2009-115/000-006

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue



Item no.: 2009-115/000-007

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray



WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green

Item no.: 2009-115/000-017

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; light green

4

Item no.: 2009-115/000-012

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange

\*

Item no.: 2009-115/000-024

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; violet

Item no.: 2009-115

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

Item no.: 2009-115/000-002

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; yellow

1.1.5.3 Marker carrier



Item no.: 2009-198 Adaptor; gray

Item no.: 2009-110

Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white

#### 1.1.5.4 Marking strip

### 1.1.6 Test and measurement

#### 1.1.6.1 Testing accessories



Item no.: 2009-174

Test plug adapter; for 4 mm Ø test plugs; for testing TOPJOB®S rail-mounted terminal blocks; gray

Item no.: 210-136

Test plug;  $2 \text{ mm } \emptyset$ ; with 500 mm cable; red

Item no.: 2009-182
Testing tap; for max. 2.5 mm²; tool-free connection for individual test wires 0.08 - 2.5 mm; gray

https://www.wago.com/2006-8033



1.1.7 Tool

1.1.7.1 Operating tool

,

<u>Item no.: 210-719</u>

Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft

Item no.: 210-721

Operating tool; Blade: 5.5 x 0.8 mm; with a partially insulated shaft; multicoloured

#### Installation notes

#### Conductor termination



All conductor types at a glance

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at:  $\underline{www.wago.com}$ 

Page 6/6 Version 13.04.2022