

**WINSTA® MIDI**  
**Linect® T-Connector, T-Distribution Connectors, 3-Pole**





	250 V/4 kV/3 $I_N$ 25 A (16 A) ①  ② Approvals	250 V/4 kV/3 $I_N$ 25 A  ② Approvals
--	--	---



Description	Color	Item No.	Pack. Unit	Color	Item No.	Pack. Unit
Linect® T-connector		Linect® T-connector, 3-pole,		T-distribution connector, 1 x plug/2 x socket		
T-distribution connector		socket - plug,		● black	770-606	50
Intermediate coupler		white housing, white cover		○ white	770-656	50
h-distribution connector	○ white	770-6223	25	● orange	770-667	50
		Suitable for 294-8013 and 294-8113 Lighting Connectors		for "flying leads", with 3rd locking lever		
				● black	770-615	50
				○ white	770-665	50
				● orange	770-670	50

Item-Specific Accessories						
		Lockout cap, for socket, separable, 12-pole			Lockout cap, for socket, separable, 12-pole	
		black 770-201 100			black 770-201 100	
		white 770-221 100			white 770-221 100	
		Lockout cap, for plug, separable, 5-pole			Lockout cap, for plug, separable, 5-pole	
		yellow 770-360 100			yellow 770-360 100	
		Coding pin, for plug (A and B coding)				
		gray 770-401 100				
Info	Dimensions					



- ② For "International Certification Organizations" and "Approvals - User Guide," see page 300.
  - ③ 5.0 mm Ø, 0.2 ... 1.2 mm plate thickness
  - ④ 6.0 mm Ø, 1 ... 2.5 mm plate thickness
- |          |          |             |
|----------|----------|-------------|
| ● black  | Coding A | (L ⊕ N)     |
| ○ white  | Coding A | (L ⊕ N)     |
| ● red    | Coding P | (L ⊕ N)     |
| ● orange | Coding R | (LON LON S) |
- For coding information, see page 284.  
Fire load data available upon request.

