

Illuminated Tactile Switch




Q-9234

TYPE: **SPL12**


SPECIFICATIONS

Rating: 50mA 12V DC
 Contact R: 100mΩ max
 Insulation R: 500V DC 100MΩ min
 Dielectric Strength: 1 Minute 1000V AC
 Operating Temperature: -25°C ~ +60°C
 Electrical Life: 5,000, 000 Cycles
 Operating Force: 300gf±50gf


Outline Drawing




Mounting



Circuitry



OFF – (ON)
(LED)



Сеть магазинов
КВАРЦ
 Радиодетали и электронные компоненты

107023, Москва, ул. Буженинова, д. 16
 телефон: (495) 963-6120
 факс: (495) 963-4994
 e-mail: quartz1@quartz1.ru

111123, Москва, шоссе Энтузиастов, д31
 телефон/факс: (495) 788-8899 *многоканальный*
 e-mail: mqz@quartz1.ru