

Han-Eco 10B-HSE-for DL-M32-glanded



Part number	19 43 110 0527
Specification	Han-Eco 10B-HSE-for DL-M32-glanded
HARTING eCatalogue	https://b2b.harting.com/19431100527

Identification

Category	Hoods/Housings
Series of hoods/housingsHan-Eco [®] B	
Type of hood/housing	Hoods
Description of hood/ housing	With integrated cable gland

Version

Locking type	Double locking lever
Size	10 B
Version	Side entry
Cable entry	1x M32

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP66
Clamping range	13 21 mm

Material properties

Material (hood/housing)	Polyamide Fibre-glass reinforced
Colour (hood/housing)	RAL 9005 (jet black)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	IEC 61984
	EN 45545-2 R22: HL1, HL2, HL3
	EN 45545-2 R23: HL1, HL2, HL3
	EN 45545-2 R24: HL1, HL2, HL3

Commercial data

Packaging size 1	
------------------	--

Product data sheet 19 43 110 0527 Han-Eco 10B-HSE-for DL-M32-glanded



Commercial data

Net weight	131.25 g
Country of origin	Germany
European customs tariff number	85389099