



3101 MALE STUD FITTINGS, HEXAGONAL, BSPP AND METRIC for metric tubing

| |  | ØD (mm) | C | E (mm) | F1 (mm) | F2 (mm) | H (mm) | K (mm) |  (kg) |
|------------|---|------------|---------|-----------|------------|------------|-----------|-----------|---|
| 3101 03 09 | | 3 | M3x0,5 | 2,5 | 8,0 | | 12,5 | | 0,003 |
| 3101 03 19 | | 3 | M5x0,8 | 3,5 | 8,0 | 2,5 | 12,5 | 8,5 | 0,004 |
| 3101 04 09 | | 4 | M3x0,5 | 2,5 | 8,0 | | 14,5 | | 0,003 |
| 3101 04 10 | | 4 | G1/8 | 5,0 | 13,0 | 3,0 | 11,5 | 14,0 | 0,007 |
| 3101 04 13 | | 4 | G1/4 | 5,5 | 16,0 | 3,0 | 10,5 | 17,5 | 0,011 |
| 3101 04 19 | | 4 | M5x0,8 | 3,0 | 8,0 | 2,5 | 14,0 | 8,5 | 0,003 |
| 3101 04 55 | | 4 | M7x1 | 5,0 | 10,0 | 2,5 | 14,0 | 11,0 | 0,004 |
| 3101 06 10 | | 6 | G1/8 | 5,0 | 13,0 | 4,0 | 13,0 | 14,0 | 0,007 |
| 3101 06 13 | | 6 | G1/4 | 5,5 | 16,0 | 4,0 | 12,5 | 17,5 | 0,010 |
| 3101 06 17 | | 6 | G3/8 | 5,5 | 20,0 | 4,0 | 13,0 | 22,0 | 0,020 |
| 3101 06 19 | | 6 | M5x0,8 | 3,0 | 10,0 | 2,5 | 16,0 | 11,0 | 0,005 |
| 3101 06 21 | | 6 | G1/2 | 7,5 | 24,0 | 4,0 | 20,0 | 26,0 | 0,039 |
| 3101 06 55 | | 6 | M7x1 | 5,0 | 10,0 | 3,0 | 16,0 | 11,0 | 0,005 |
| 3101 06 60 | | 6 | M10x1 | 5,0 | 13,0 | 4,0 | 13,0 | 14,0 | 0,030 |
| 3101 06 67 | | 6 | M12x1,5 | 5,5 | 15,0 | 4,0 | 13,0 | 16,0 | 0,009 |
| 3101 08 10 | | 8 | G1/8 | 4,5 | 13,0 | 5,0 | 20,5 | 14,0 | 0,011 |
| 3101 08 13 | | 8 | G1/4 | 5,5 | 16,0 | 6,0 | 19,5 | 17,5 | 0,015 |
| 3101 08 17 | | 8 | G3/8 | 5,5 | 20,0 | 6,0 | 18,0 | 22,0 | 0,022 |
| 3101 08 21 | | 8 | G1/2 | 7,5 | 24,0 | 6,0 | 16,5 | 26,0 | 0,039 |
| 3101 08 60 | | 8 | M10x1 | 5,0 | 13,0 | 5,0 | 21,0 | 14,0 | 0,012 |
| 3101 08 67 | | 8 | M12x1,5 | 5,5 | 15,0 | 5,0 | 21,0 | 16,0 | 0,030 |
| 3101 10 13 | | 10 | G1/4 | 5,5 | 16,0 | 7,0 | 23,0 | 17,5 | 0,017 |
| 3101 10 17 | | 10 | G3/8 | 5,5 | 20,0 | 8,0 | 19,5 | 22,0 | 0,020 |
| 3101 10 21 | | 10 | G1/2 | 7,5 | 24,0 | 8,0 | 18,5 | 26,0 | 0,032 |
| 3101 12 13 | | 12 | G1/4 | 5,5 | 19,0 | 7,0 | 27,5 | 21,0 | 0,027 |
| 3101 12 17 | | 12 | G3/8 | 5,5 | 20,0 | 9,0 | 27,0 | 22,0 | 0,029 |
| 3101 12 21 | | 12 | G1/2 | 7,0 | 24,0 | 10,0 | 22,5 | 26,0 | 0,035 |
| 3101 14 17 | | 14 | G3/8 | 5,5 | 22,0 | 9,0 | 29,5 | 24,0 | 0,040 |
| 3101 14 21 | | 14 | G1/2 | 7,0 | 24,0 | 10,0 | 28,0 | 26,0 | 0,045 |