

EK EKOE 180 G



Sample photo

Order symbol: EKOE 180 G
Product nbr: 2538040
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074013576
El. number:
Finland: 3425419
Italy: 7501140
Sweden: 2538040
Norway:

Including: Flanged Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

| Dimensions: | | Length | Width | Height | Rating: |
|-------------------------------|--|-------------------------|-------|--------|--|
| mm: | | 280 | 280 | 180 | Ingress Protection (EN 60529): IP 66/67 |
| inch: | | 11.0 | 11.0 | 7.1 | Impact Resistance (EN 62262): IK 08 |
| Materials: | | | | | Electrical insulation: Totally insulated |
| Material: | | Polycarbonate | | | Halogen free (DIN/VDE 0472, Part 815): Yes |
| Base colour: | | RAL 7035 | | | UV resistance: UL 508 |
| Cover colour: | | RAL 7035 | | | Flammability Rating (UL 746 C 5): UL 746C 5V |
| Cover screws material: | | Polyamide | | | Glow Wire Test (IEC 695-2-1) °C: 960 |
| Cover screws colour: | | Grey | | | NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12 |
| Gasket material: | | Polyurethane | | | |
| Temperatures: | | | | | Certificates: |
| Short term: | | -40 ... 120 °C | | | Germanischer Lloyd (GL) |
| Continuous: | | -40 ... 80 °C | | | Underwriters Laboratories |
| Short term: | | -40 ... 250 °F | | | Det Norske Veritas |
| Continuous: | | -40 ... 175 °F | | | Bureau Veritas |
| Accessories: | | | | | Fimko |
| EKOE | | Base, PC | | | Lloyds Register of Shipping (LR) |
| EKO 30-G | | Cover | | | Europe EN 62208: 2003 |
| EKO 80-G | | Cover | | | UL Canada |
| EKO 30-T | | Cover | | | Gost R |
| EKO 80-T | | Cover | | | |
| EKOVT | | Mounting plate | | | |
| EKOXT | | Mounting plate Pertinax | | | |
| EKV 22 | | DIN-35 Mounting rail | | | |
| EKOZR | | Extension frame | | | |

