



### fitted with

work equipment  
 connected load  
 power consumption  
 system of protection  
 class of protection  
 technology  
 usage  
 luminaire body  
 lamp cover  
 tubular sections  
 balance of articulation joints  
 weight (net)  
 mains lead  
 fastening


### special features

3 x Light-emitting diode  
 light colour daylight white, 5500-6000 K, Color Rendering Index (CRI)=72  
 Energy efficiency category A+  
 without  
 24 V; AC/DC  
 approx. 6 W  
 IP 65  
 III  
 switchable  
 switch  
 aluminium, anodised, black  
 glass screen  
 flexible metal tube, black  
 friction  
 approx. 1.3 kg  
 approx. 3.0 m; with free stranded wires  
 screw-down flange, magnetic base (accessory), table clamp (accessory), wall bracket (accessory)  
 Spot with a 10° angle of radiation

### illuminance

measuring conditions: d=50cm

Em: 4086 lx  
 Emax: 27500 lx  
 Emin: 440 lx



### luminous intensity

