



BU-3110410-@ (Insulated, Stackable Banana Plug)



- The BU-3110410-@ is a fully insulated, stackable 4mm Banana plug to be used with Mueller's 10 AWG Coolfelx45 test lead wire (WI-M-10-@). It can be plugged into any standard 4mm banana jack that accepts shrouded banana plugs. The Jack end will accept any shrouded, un-shrouded, or retractable 4mm banana. The banana plug has a plastic safety tip.
- Overall length of 2.1" (53mm), Width of 0.73" (19mm), and Height of 0.45" (11mm)
- Material:
 - Banana – Nickel plated beryllium copper
 - Insulator – Polypropylene
- Rating:
 - Current – 45 Amps
 - 600 Volts
- Color: The "@" in the model number indicates color.
Available colors are: -0 Black, -2 Red
- RoHS 3 Compliant, CE Certified

Assembly Instructions



- 1) Thread wire thru offset hole of housing and solder into cross hole in Banana Plug.



- 2) Align the Banana plug into the housing as shown



- 3) Snap together