

# PLASTIC CABLE GLANDS


## HSK-K-PVDF PG



Material	PVDF V0 according to UL 94
Seal	FKM
Protection	IP 68 – 10 bar / IP 69K (NEMA 6 – 150 PSIG) with additional O-Ring
Operating Temperature	-35 °C – 150 °C (-31 °F – 302 °F)
Colors	nature



- // With additional pre-assembled O-Ring upon request
- // Suitable O-Ring on page 88
- // Other sealing materials e.g. silicone upon request
- // Other colors upon request



AG	∅k mm	GL mm	H mm		mm	Number
PG 7	3–6,5	8	21	15		1.299.0700.14
PG 7	2–5	8	21	15		1.299.0700.15
PG 9	4–8	8	22	19		1.299.0900.14
PG 9	2–6	8	22	19		1.299.0900.15
PG 11	5–10	8	25	22		1.299.1100.14
PG 11	3–7	8	25	22		1.299.1100.15
PG 13,5	6–12	9	27	24		1.299.1300.14
PG 13,5	5–9	9	27	24		1.299.1300.15
PG 16	10–14	10	28	27		1.299.1600.14
PG 16	7–12	10	28	27		1.299.1600.15
PG 21	13–18	11	31	33		1.299.2100.14
PG 21	9–16	11	31	33		1.299.2100.15
PG 29	18–25	11	39	42		1.299.2900.14
PG 29	13–20	11	39	42		1.299.2900.15
PG 36	22–32	13	48	53		1.299.3600.14
PG 36	20–26	13	48	53		1.299.3600.15
PG 42	32–38	13	49	60		1.299.4200.14
PG 42	25–31	13	49	60		1.299.4200.15
PG 48	37–44	14	49	65		1.299.4800.14
PG 48	29–35	14	49	65		1.299.4800.15

