

PTRO-0630 - PTRO

General Part Information	
Product Description	PTRO-0630
Article Number	32986
POPNut Type	i PTRO
Standard Bulk Pack Quantity	4,000

Geometry / Dimensions	
Thread Size	M6
Body Type (open / closed)	i Open
Body Features	i Round
Body Length (mm)	14.30
Min. Grip Thickness (mm)	0.50
Max. Grip Thickness (mm)	3.00
Head Style	i Reduced Head
Hole Diameter (mm)	9.00
Head Diameter (mm)	9.80
Head Thickness (mm)	0.80
Barrel Diameter (mm)	8.90

Material / Weight	
Material	i Stainless Steel 302
Weight per thousand (kg)	3.2

