

CARDMASTER ABS 30/25-3



Order symbol: ABS 30/25-3
Product nbr: 7585019
Description: Enclosure, ABS
Remarks: Smoked transparent hinged cover

EAN: 6418074056795
EI. number:
 Finland: 3438245
 Electric No. Denmark: 8212016774
 Electric No. Sweden: 7585019

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	320	260	129	FP 30/25 Front plate (aluminium)
inch:	12.6	10.2	5.1	FC PC 30/25 Frame of PC front plate
Materials:				Rating:
Material:	ABS			Ingress Protection (EN 60529): IP65
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07
Cover colour:	Smoked grey			Electrical insulation: Totally insulated
Gasket material:	EPDM & PUR			Halogen free (DIN/VDE 0472, Part 815): 1
Temperatures:				Flammability Rating: UL 94 HB
Temperature °C (short term):	-40 ... 80 °C			Glow Wire Test (IEC 695-2-1) °C: 650
Temperature °C (continuous):	-40 ... 60 °C			NEMA Class: NEMA 1, 3, 3R, 12, 13
Temperature °F (short term):	-40 ... 175 °F			
Temperature °F (continuous):	-40 ... 140 °F			
Accessories:				
MP 30/25	Mounting plate			

