

SOLID ABS 2828 18 G



Sample photo

Order symbol: ABS 2828 18 G
Product nbr: 5880372
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074039071
EI. number:
 Finland: 3423765
 Electric No. Italy: 7410145
 Electric No. Sweden: 2539719

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	278	278	180	EKOXT	Mounting plate isolated
inch:	10.9	10.9	7.1	EKV 22	DIN-35 Mounting rail
				EKOZR	Extension frame

Materials:		Rating:
Material:	ABS	Ingress Protection (EN 60529): IP66/IP67
Base colour:	RAL 7035 -light grey	Impact Resistance (EN 62262): IK08
Cover screws material:	Polyamide	Electrical insulation: Totally insulated
Cover colour:	RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour:	Grey	Flammability Rating: UL 94 HB
Gasket material:	Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 650
		NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Temperatures:		Certificates:
Temperature °C (short term):	-40 ... 80 °C	SGS Fimko
Temperature °C (continuous):	-40 ... 60 °C	
Temperature °F (short term):	-40 ... 175 °F	
Temperature °F (continuous):	-40 ... 140 °F	

Accessories:	
EKOVT	Mounting plate

