

MNX PC 200/88 XHT



Sample photo

Order symbol: PC 200/88 XHT
Product nbr: 6013930
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074051943
EI. number:
 Finland: 3435266
 Electric No. Denmark: 8212023071
 Electric No. Sweden: 6013930

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	255	180	88	MIN 15 DIN-15 Mounting rail
inch:	10.0	7.1	3.5	MIN 20 DIN-15 Mounting rail
				MIV 15 DIN-35 Mounting rail
				MIV 20 DIN-35 Mounting rail

Materials:	
Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	Smoked grey
Cover screws colour:	Black
Gasket material:	Polyurethane

Rating:
Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5"
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

Temperatures:	
Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Accessories:
MIV 200
Mounting plate (Galvanized steel)

Certificates:
SGS Fimko

