


KSR16-L0-08-10-16-22

Roller chain idler sprocket unit

Schaeffler ID:
0009517490000

Roller chain idler sprocket units KSR...-L0...-22, sprocket made from plastic

Technical information



Main Dimensions & Performance Data

d	16.2 mm	Bore diameter
d	0.1 mm	Upper tolerance
d	0 mm	Lower tolerance
C ₁	7 mm	Thickness of sprocket
D ₀	65.1 mm	Pitch circle diameter (gearing)
D _k	70.5 mm	Tip diameter (gearing)
	0.097 kg	Weight

Dimensions

C ₂	1.1 mm	Chamfer width
D	40 mm	Outside diameter
C	18.1 mm	Width, outer ring
R	48 mm	Heeldiameter sprocket
B	18.3 mm	Width inner ring

Mounting dimensions

p	0.5 inch	Tooth set
z	16	Number of teeth
	x	ISO chain
	x	ANSI chain