



Soldering Station with LCD Display ESD Safe



Backlit LED Display

Iron Holder
With Safety Guard

Storage Compartment



Standard Pointed
Tip Included

SOLDERING STATION WITH LCD DISPLAY, ESD SAFE	
RATED VOLTAGE RANGE	110-130V or 220-240V
RATED POWER INPUT	58W
TEMPERATURE RANGE	160-550°C (320-1020°F)
TIP	Standard Pointed Tip
POWER SOURCE	Corded Electrical
WEIGHT	0.75 (1.6 lbs.)

ADDITIONAL TIPS	
17400-N91	
17400-N92	
17400-N93	
17400-N94	
17400-N95	

Part #	Description	Price
17405	Soldering Station with LCD Display ESD Safe	\$54.95

Compact & Convenient Soldering Station

The Aven 30W temperature controlled soldering station features a compact design that takes up minimal bench top space, an LCD display with blue backlight, safety guard iron holder, and a high quality ceramic heater that heats quickly and is designed for reliable, long-lasting use. The temperature range, from 160° to 550° C, is suitable for manual mounting and reworking of SMD components, audio equipment, RC hobbies and more. Soldering iron features a long life replaceable fine tip and comes with a 1.2m (4-foot) heavy-duty power cord. This exceptional soldering station also includes a recessed tip cleaning area with solid sponge for cleaning the iron tip as well as a small drawer in the base of the station for storing spare parts.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aven:](#)

[17405](#)