



LED Dual Gooseneck Spotlight Illuminator

Rotatable and Flexible
22 3/8" Gooseneck Arms



LED Lighting
Cool Operating Temperature

Dual Adjustment
Adjustable Light Intensity Knobs

Versatile and Flexible

Aven's LED Dual Gooseneck Spotlight Illuminator gives users the ability to inspect at any angle and at any working distance. Each flexible gooseneck arm can be swiveled and bent to the desired position, and stays in place. Use one LED illuminator—or both—and control the light intensity of each illuminator as desired. Optional Ultra-Violet Gooseneck Arms available separately.

- Versatile, adjustable illumination at any angle
- 6500K cool light LED illuminator
- Add illumination to difficult to reach areas
- 23-3/8" (568mm/each) long dual gooseneck lights
- Metal framework intensity control box with light adjustment knobs for each light
- UV Dual Gooseneck Illuminators sold separately



LED Cool Light Illumination (UV Illuminators Available Separately)



Illuminate and Overlap Spotlights at Any Angle



Light Adjustment Knobs for Each Illuminator and On/Off Switch on Metal Base

| Aven LED Dual Gooseneck Spotlight Illuminator | |
|---|--|
| Item # | Description |
| 26200B-221 | LED Dual Gooseneck Spotlight Illuminator |

| Optional Add-Ons | |
|------------------|---|
| Item # | Description |
| 26200B-221-GNUV | UV Dual Gooseneck Spotlight Illuminator |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aven:](#)

[26200B-221](#)