

Datasheet

ENGLISH

Stock No: 257-8381

RS PRO 7094796 Analogue Vacuum Gauge, Maximum Pressure Measurement Obar, Gauge Outside Diameter 100mm



Product Details

100mm Diameter Pressure and Vacuum Gauges - Stainless Steel Construction

Suitable for corrosive environments and gaseous or liquid media that will not destruct the pressure system

Laminated Safety Glass Window

316TI Stainless Steel Element & Movement

304 stainless Steel case with G 1/2 in. BSPM connection

Bottom entry connection

Ambient Operating Temperature between -20 and +60°C

Operating Temperature (Medium) +100°C

1.6 Per DIN 16005 Accuracy Class



ENGLISH

Specifications:

Pressure Gauge Type	Bottom Entry
Maximum Pressure Measurement	0bar
Minimum Pressure Measurement	-1bar
Gauge Outside Diameter	100mm
Connection Size	BSP G 1/2
Maximum Operating Temperature	+60°C
Minimum Operating Temperature	-20°C
Case Material	Stainless Steel