

Search by SKU, Product Name or Keyword

SEARCH

CART

[Products](#) [Contact Us](#) [Catalogs](#) [Sample Program](#) [Free CAD](#)

[Home](#) [Fiber, Wire & Cable Manage...](#) [Grommets](#) [Open Grommets](#)



Open Hole Grommet, Black, TPV, .219 in ID, .430 in OD, .217 in Thick, .315 in Hole Dia

In Stock !

Item Code: HG-3.5

Black TPV Hole Grommet convert raw-edged .219 in (5.6 mm) diameter holes in panels and enclosures into smooth openings to protect up to N/A cables as they pass through.



Description	Quantity	Unit Price	Options
Type : Hole Grommet Compatible Hole Diameter : .315 in (8 mm) Inside Diameter : .219 in (5.6 mm) Panel Thickness : .063 in (1.6 mm) Material Flammability Standard : UL94 HB Overall Diameter : .430 in (10.9 mm) Overall Height : .217 in (5.5 mm) Brand : Richco Hole Diameter : .315 in (8 mm)	Standard Pack: 1000 Buy in multiples of: 1000 <hr/> 1000 : \$0.1671 <hr/> 5000 : \$0.1324 <hr/> 10000 : \$0.1139 <hr/> 25000 : \$0.1034 <hr/> 50000 : \$0.0899 <hr/> 100000 : \$0.081	<input type="text" value="1000"/> <hr/> <p style="text-align: center;">Add to Cart</p> <hr/> <input type="button" value="Request CAD"/> <hr/> <input type="button" value="Free Sample"/> <hr/> <input type="button" value="Request Quote"/>	

[Downloads](#)

[Print Page](#)

Products you might be interested in



Open Hole Grommet, Black, TPV, .125 in ID, .313 in OD, .252 in Thick, .190 in Hole Dia



Open Hole Grommet, Black, TPV, .500 in ID, .954 in OD, .280 in Thick, .748 in Hole Dia



Open Hole Grommet, Black, TPV, .313 in ID, .630 in OD, .276 in Thick, .433 in Hole Dia



Open Hole Grommet, Black, TPV, .970 in ID, 1.500 in OD, .313 in Thick, 1.240 in Hole Dia

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Essentra:](#)

[HG-3.5](#)