



# DUAL-IN-LINE SOCKETS

## SERIES 210, 222, 223 • SOLDER TAIL AND WRAPOST • CLOSED FRAME



- Closed frame insulator withstands high mechanical impact
- Available with standard solder pins, 2-level or 3-level wrapposts
- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details
- Series 210, 222 and 223 use MM #1001, #0088 or #0089 pins. See pages 165 & 198 for details
- Insulators are high temperature thermoplastic, suitable for all soldering operations
- For Electrical, Mechanical and Environmental Data, see page 264 for details



Total number of pins				Quantity per tube	ORDERING INFORMATION								
	A	B	C		Solder Tail	L = 9,4 (2 Level Wrappost)	L = 12,96 (3 Level Wrappost)						
6	7,6	7,62	10,1	67	210-XX-306-41-001000	222-XX-306-41-001000	223-XX-306-41-001000						
8	10,1	7,62	10,1	50	210-XX-308-41-001000	222-XX-308-41-001000	223-XX-308-41-001000						
10	12,6	7,62	10,1	40	210-XX-310-41-001000	222-XX-310-41-001000	223-XX-310-41-001000						
14	17,7	7,62	10,1	28	210-XX-314-41-001000	222-XX-314-41-001000	223-XX-314-41-001000						
16	20,3	7,62	10,1	25	210-XX-316-41-001000	222-XX-316-41-001000	223-XX-316-41-001000						
18	22,8	7,62	10,1	22	210-XX-318-41-001000	222-XX-318-41-001000	223-XX-318-41-001000						
20	25,3	7,62	10,1	20	210-XX-320-41-001000	222-XX-320-41-001000	223-XX-320-41-001000						
22	27,8	7,62	10,1	18	210-XX-322-41-001000	222-XX-322-41-001000	223-XX-322-41-001000						
24	30,4	7,62	10,1	16	210-XX-324-41-001000	222-XX-324-41-001000	223-XX-324-41-001000						
22	27,8	10,16	12,7	18	210-XX-422-41-001000	222-XX-422-41-001000	223-XX-422-41-001000						
24	30,4	10,16	12,7	16	210-XX-424-41-001000	222-XX-424-41-001000	223-XX-424-41-001000						
24	30,4	15,24	17,7	16	210-XX-624-41-001000	222-XX-624-41-001000	223-XX-624-41-001000						
28	35,5	15,24	17,7	14	210-XX-628-41-001000	222-XX-628-41-001000	223-XX-628-41-001000						
32	40,6	15,24	17,7	12	210-XX-632-41-001000	222-XX-632-41-001000	223-XX-632-41-001000						
36	45,7	15,24	17,7	11	210-XX-636-41-001000	222-XX-636-41-001000	223-XX-636-41-001000						
40	50,8	15,24	17,7	10	210-XX-640-41-001000	222-XX-640-41-001000	223-XX-640-41-001000						
64	81,2	22,86	25,3	6	210-XX-964-41-001000	222-XX-964-41-001000	223-XX-964-41-001000						
XX=Plating Code See Below													
SPECIFY PLATING CODE XX =					11	13	91	93	99	41	43	44	47
Sleeve (Pin)					0,25µm Au	0,25µm Au	5,08µm Sn/Pb	5,08µm Sn/Pb	5,08µm Sn/Pb	5,08µm Sn	5,08µm Sn	5,08µm Sn	5,08µm Sn
Contact (Clip)					0,25µm Au	0,76µm Au	0,25µm Au	0,76µm Au	2,54µm Sn/Pb	0,25µm Au	0,76µm Au	2,54µm Sn	Au Flash