

FEATURES

- Tubular MCC indicator light
- BA9s base
- 7,000 hours life
- Luminosity of 6.3lm
- Voltage rating of 24V
- Current rating of 80mA
- Length of 28mm
- Diameter of 10mm
- Conforms to ANSI/ESD S20.20:2014 and BS EN 61340-5-1:200 on electrostatic discharge

BA9s Indicator Light, Clear, 24 V, 80 mA, 7000h

RS Stock No.: 360-7777



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Need to illuminate an instrumentation panel? Comprising a clear incandescent bulb, this tubular MCC indicator light from the RS PRO range will give you 7,000 hours of illumination. It features a voltage rating of 24 V and a current rating of 80 mA. In terms of luminosity, it provides 6.3 lm.

General Specifications

Lamp Base	Ba9s/13
Lamp Size	T10
Lens Colour	Clear
Luminosity	6.3lm
Life hours	7000h
Filament Type	C-2F/Vacuum Type
Housing Material	Glass
Applications	Automotive industry; Gambling machine industry; Car indicator; Garden lights; Paper lanterns; Battery-powered flashlights

Electrical Specifications

Voltage Rating	24V
Current Rating	80mA+10%
MSCP	0.5 CP+20%
Light Output	6.3lm

Mechanical Specifications

Diameter	10mm \pm 1mm
Length	28mm \pm 2mm

Approvals

Compliance/Certifications

RoHS, ANSI/ESD S20.20:2014, BS EN 61340-5-1:200



Drawing (mm):

