

SVS ECO VALVE PLUG FORM BI 11MM 230V

2+PE field-wireable M16x1.5



Form BI (11 mm)
250 V AC/DC
without components
metric
field-wireable

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.


[Link to Product](#)

Illustration

stay connected



Height: 31 mm



Product may differ from Image

Approvals

EAC

ChinaRoHS25

Form	
Form	30005
Technical Data	
Operating voltage	max. 250 V AC/DC
Operating current per contact	max. 10 A
Configuration	2 contacts + PE
Connection cross section	0.5...1.5 mm ²
Sealing range (cable Ø)	6...8 mm
Locking of ports	M3 (recommended torque 0.4 Nm)
Compression gland	M16×1.5 mm
Contact figure	Cable outlet can be turned in 180° steps
Protection	IP65 inserted and tightened (EN 60529)
General data	
Temperature range	-40...+90 °C
Material (gasket)	NBR
Mounting method	inserted, tightened
Commercial data	
country of origin	HU
customs tariff number	85366990
EAN	4048879187046
eClass	27279221
Packaging unit	1