

**PICCOLO PC H 95 G**



Sample photo

**Order symbol:** PC H 95 G  
**Product nbr:** 8724315  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074002273  
**EI. number:**  
 Finland: 3423417  
 Electric No. 8212001653  
 Denmark:  
 Electric No. Italy: 7201050  
 Electric No. Sweden: 2536826

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:	
mm:	170	140	95	CHM-3	DIN-35 Mounting rail
inch:	6.7	5.5	3.7	DH-3	DIN-35 Mounting rail
				FP 22046	Wall fastening lug (4 pcs)

Materials:		Rating:
<b>Material:</b>	Polycarbonate	Ingress Protection (EN 60529): IP66/67
<b>Base colour:</b>	RAL 7035 -light grey	Impact Resistance (EN 62262): IK08
<b>Cover screws material:</b>	Polyamide	Electrical insulation: Totally insulated
<b>Cover colour:</b>	RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
<b>Cover screws colour:</b>	Grey	UV resistance: UL 508
<b>Gasket material:</b>	Polyurethane	Flammability Rating: UL 746C 5V
		Glow Wire Test (IEC 695-2-1) °C: 960
		NEMA Class: NEMA 1, 4X, 6, 6P, 12, 13

Temperatures:		Certificates:
<b>Temperature °C (short term):</b>	-40 ... 120 °C	Germanischer Lloyd (GL)
<b>Temperature °C (continuous):</b>	-40 ... 80 °C	SGS Fimko
<b>Temperature °F (short term):</b>	-40 ... 250 °F	Gost R
<b>Temperature °F (continuous):</b>	-40 ... 175 °F	

Accessories:	
H-MP	Mounting plate

