

## FEATURES

- Indicator light
- Wedge groove base
- 10,000 hours life
- Luminosity of 3.53lm
- Voltage rating of 28V
- Current rating of 40mA
- Length of 20mm
- Diameter of 5mm
- Conforms to ANSI/ESD S20.20:2014 and BS EN 61340-5-1:200 on electrostatic discharge

## Wedge Indicator Light, Clear, 28 V, 40 mA, 10000h

RS Stock No.: 655-9744



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Looking for an indicator light to use in an automotive application or within an instrumentation panel? This wedge indicator light from the RS PRO range offers you an impressive 10,000 hours of life. It provides luminosity of 3.53 lumens, with a voltage rating of 28 V and a current rating of 40 mA.

## General Specifications

<b>Lamp Base</b>	Wedge
<b>Lamp Size</b>	T1 ½
<b>Lens Colour</b>	Clear
<b>Luminosity</b>	3.53lm±20%
<b>Life hours</b>	10,000h
<b>Filament Type</b>	Vacuum Type
<b>Housing Material</b>	Glass
<b>Applications</b>	Automotive industry; Gambling machine industry; Car indicator; Garden lights; Paper lanterns; Battery-powered flashlights

## Electrical Specifications

<b>Voltage Rating</b>	28V
<b>Current Rating</b>	40mA+10%
<b>Light Output</b>	3.53lm

## Mechanical Specifications


<b>Diameter</b>	5.0mm
<b>Length</b>	20.0mm

## Approvals

### Compliance/Certifications

RoHS, ANSI/ESD S20.20:2014, BS EN 61340-5-1:200



RS Stock No.		6559744
<i>DRAWING - I</i>		
		
Unit : mm		
1. Structure	Bulb Type	T1 1/2 Clear
	Bulb Diameter	Ø5.0Max.
	Length	20.0Max
	Base Type	Wedge Base
2. Design Characteristics	Voltage	28V
	Amperage	40mA±10%
	Filament Type	Vacuum type
	Luminous Flux	3.53Lm±20%
	Life Hours	10,000Hrs