


1 2 3 4 5 6 7 8

A

A

B

B



### SPECIFICATION


- 1. Rated Voltage.....9Vp-p Square Wave
- 2. Operating Voltage.....3~15Vp-p Square Wave
- 3. Max. Rated Current.....3mA
- 4. Min. Sound Pressure Level.....72dB/4KHz/9Vp-p Square Wave/10cm
- 5. Capacitance at 100Hz ..... 12000 ± 30% pF
- 6. Resonant Frequency.....4.0 ± 0.5 KHz
- 7. Shell Material/Color.....PBT/Black
- 8. Operating Temperature.....-20~+70°C
- 9. Store Temperature.....-40~+85°C
- 10. Weight.....0.5g

C

C

D

D



E

E

F

F

				<b>KEPO</b> NINGBO KEPO ELECTRONIC CO.,LTD <a href="http://www.chinaacoustic.com">http://www.chinaacoustic.com</a>	
No.	DESCRIPTION	APPROVED	DATE	Piezo Transducer quartz-1	
TOLERANCES UNLESS NOTED OTHERWISE X .X .XX . .XXX . 90° FORMED +2° ANGLES -1°		APPROVALS	DATE	KPT-1040	
FIRST ANGLE PROJECTION		DRAWN		UNIT	DWG NO.
CHECKED		CHECKED		mm	OEM2435
APPROVED		APPROVED	06.11.24	SCALE	SHEET
				NOT TO SCALE	VER 1.0

1 2 3 4 5 6 7 8