

## **Datasheet**

**ENGLISH** 

## RS Pro 2, 3 & 5 WAY 2 HOLE FLANGE MOUNT PLUG 25A IP68



## Specifications:

From RS Pro, these threaded plugs are serious contenders for your application. This particular model has a bigger and stronger shell complimented by its 2 hole flange-mounted connection. That coupled with the IP68 rating, makes sure that this industrial connector excels in harsh environments. When choosing a male connector, this version should really be one you consider.



## ENGLISH

Coupling Type	Threaded Coupling
IP Rating	IP68
Material	Plastic
Shell	Nylon66, fire resistance:V-0
Insert Material	PPS max temperature 260°C, fire resistance:V-0
Contact Material	Brass with gold plating
Termination	Solder/Screw/Crimp
Cable outer diameter range	I: 4.5-7mm II: 7-12mm
Mating cycle	>500
Temperature range	-25℃~+85℃
Insulation resistance $M\Omega$	2000