LED Flexible Tape - LINEO LINE 10M Kit

Designed for architectural bespoke lighting, LINEO IP67, 10M, 50W, Kit provides a continuous seamless bright light with the capability of bending

									,	
to	а	tiaht	12cm	diameter.	Perfect	for your	interior	feature	IFD I	
	ч	ngm	120111	alameter.	1 011001	101 7001	111101101	icaioic		

TINEO LINE 10M KH

LINEO LINE TOWN KIT							
Part Code	LIN-5700-IP67-KIT	LIN-2700-IP67-KIT					
Lumen Output	320lm	320lm					
Input Voltage	24Vdc	24Vdc					
Power per metre	5W	5W					
Cuttable length	100mm	100mm					
LED Qty	60 per mtr	60 per mtr					
IP	IP67	IP67					
Beam Angle	160°	160°					
CCT	5700K	2700K					
Dimensions	18 x 9mm	18 x 9mm					















Product Features

- ★ Built to customer specification ready for installation
- ★ Seamless bright light with new design of connectors
- ★ Flat profile for crisp feature light interior design
- ★ Continuous length up to 10 metres











