

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200310049](#)
Status: **Active**
Overview: [Brad Nano-Change \(M8\) Products](#)
Description: Nano-Change (M8) Receptacle, 4 Poles, M8 x 0.5 Mounting Threads, Female (Straight) to 22 AWG Leads, 0.30m (11.81") Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Receptacles
 Series [120031](#)
 IP Rating IP67
 NEMA Rating NEMA 6
 Overview [Brad Nano-Change \(M8\) Products](#)
 Product Name Nano-Change (M8)
 Type Single Ended (pigtail)
 UPC 883906177928

Physical

Coupling Type Internal Thread
 Gender Female
 Keyway None
 Length 0.30m
 Material - Component Nickel-plated Brass
 Mounting Thread Size M8 x 0.5
 Net Weight 10.660/g
 Orientation Straight
 Panel Mount Front
 Poles 4
 Temperature Range - Operating -25°C to +90°C
 Wire Size AWG 24
 Wire/Cable Type Leads

Electrical

Current - Maximum per Contact 4.0A
 Voltage - Maximum 60V AC / 75V DC

Material Info

Engineering Number 4R4F30E02C3003

Reference - Drawing Numbers

Sales Drawing 4RXF30XXXXXXXX3

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

China RoHS

Search Parts in this Series

[120031](#) Series