


NEUTRIK
[Home](#)
[Products](#)
[About us](#)
[Contact](#)
[Support](#)

[Products](#) > [Video](#) > [Phono \(RCA\)](#) > [Phono \(RCA\) Chassis Connectors](#) > NF2D-B-9

[print](#)

NF2D-B-9





Phono socket in black chrome D-shape housing, white isolation washers, solder version.

Features & Benefits

- Precisely machined to our demanding quality standards
- Gold plated contacts



Downloads

-  [Product Guide 2012, 03 Plugs+Jacks](#)
-  [Drawing NF2D](#)
-  [Drawing NF2D](#)
-  [3D File NF2D](#)

Technical Information [hide](#)

Product

| | |
|-----------------|----------|
| Title | NF2D-B-9 |
| Connection Type | RCA |
| Gender | female |

Electrical

| | |
|------------------------------|--------------------------|
| Capacitance between contacts | ≤ 9 pF |
| Contact resistance | $<5G$ m Ω (inner) |
| Dielectric strength | 0,5 kVdc |
| Insulation resistance | < 5 G Ω |
| Rated current per contact | 16 A |
| Rated voltage | 50 V |

Mechanical

| | |
|--------------------|------------------------|
| Lifetime | > 2000 mating cycles |
| Wiring | Solder contacts |
| Mounting direction | front |
| Chassis shape | D |

| Material | |
|---------------------|---------------------------|
| Contact plating | 5 µm Au over 5 µm Ni |
| Contacts | Brass (CuZn39Pb3) |
| Shell | Zinc diecast (ZnAl4Cu1) |
| Environmental | |
| Flammability | UL 94 HB |
| Standard compliance | IEC 601-14 |
| Protection class | IP 40 |
| Solderability | Complies with IEC 68-2-20 |
| Temperature range | -30 °C to +80 °C |

Accessories



CAS-DUMMY



DSS-*



MFD



NDP



SCDP-*



SCDX

