







-  PRODUCTS ▾
-  DISTRIBUTOR INVENTORY
-  INDUSTRIES ▾
-  SUPPORT ▾
-  NEWS & EVENTS ▾
-  ABOUT US ▾

3455RC 01000226









[Products](#) > [Sensors](#) > [Humidity, Thermal & Flexible Heater Products](#) > [Thermostats/Thermal Switches](#) > [Commercial > Automatic Reset](#) > [3455RC Series](#) > [3455RC 01000226](#)

Overview



3455RC Redi-Temp Series Ceramic Automatic Reset Thermostats.

Shipped from stock, the 3455RC Series thermostats are often suitable for applications such as copy machines, power supplies, telecommunications and ovens. UL, CSA and European approval agencies listings available.

-  [view all 3455RC 01000226 literature](#)
-  [view distributor inventory](#)
-  [sample request](#)
-  [email support](#)
-  [get support](#)
-  [email sales](#)
-  [find a distributor](#)
-  [email this page](#)




Technical Specifications

Functional Properties	Open on rise	Reset Type	Automatic
Operating Temperature	0 °C to 260 °C [32 °F to 500 °F]	Amperage	15 A/10 A resistive max.
Voltage	120 Vac/240 Vac	Open Temperature	51.7 °C [125 °F]
Open Tolerance	2.8 °C [5 °F]	Close Temperature	35.0 °C [95 °F]
Close Tolerance	4.4 °C [8 °F]	Environmental Exposure Range	-20 °C to 287 °C [0 °F to 550 °F]

[View More](#)

View documents in: English ▾

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 Commercial Thermostats	Datasheet	English	756KB
 Thermostats Line Guide	Product Line Guide	English	444KB
 Thermal Sensors	Product Range Guide	English	2MB

Product Features

- Cost effective
- Rivet sleeve construction
- High profile
- High temperature
- High current

Applications

- Copy machines
- Power supplies
- Telecommunications
- Office copy machines
- Ovens

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)


[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

English 

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.