



## NYS224C-\*

2 pole 1/4" plug, diecast handle with color coding ring and rubber flex relief

\*: 0-Black, 2-Red, 4-Yellow, 5-Green, 6-Blue



### Technical Information [hide](#)

<b>Product</b>	
Title	NYS224C-*
Connection Type	Plug
Gender	male
<b>Electrical</b>	
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Contact resistance	depends on mating connector
Rated current	depends on mating connector
<b>Mechanical</b>	
Cable O.D.	≤ 6 mm
Lifetime	1000 mating cycles
Wiresize	24 AWG
<b>Material</b>	
Contact plating	2 μm Ni
Contacts	Brass (CuZn39Pb3)
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel
Insulation	Thermoplastic
Strain relief	Crimp type SnCe plated

Environmental

Solderability

Complies with IEC 68-2-20

Temperature range

-20 °C to +70 °C

---

---

Data subject to change without prior notice. © 2012 NEUTRIK AG ® ALL RIGHTS RESERVED

**REAN**<sup>®</sup>  
REAN a brand of Neutrik AG