



 Deutsche Version

[Home](#)
[About Us](#)

Products

Audio

[Video](#)

[Lighting](#)

[Data Connectors](#)

[Industrial](#)

[Support](#)

[News](#)

[Sitemap](#)

Search

PRODUCTS ONLY

Search

© Neutrik® AG
All rights reserved
[Legal Notices](#)



Audio

Jacks

[back](#)

NYS240BG

Product

Connector Type Jack

Gender female

Electrical

Contact resistance < 10 mΩ

Dielectric strength 0,5 kVdc

Rated current per contact 1 A

Mechanical

Cable O.D. ≤ 4.3 mm

Insertion force ≤ 20 N

Withdrawal force > 10 N

Lifetime 1000 mating cycles

RW / Straight no

Material

Contact plating 0.2 μm Au

Contacts Brass (CuZn39Pb3)

Insert Polyamide (PA 6 30 % GR)

Shell Brass (CuZn39Pb3) Black

Strain relief CRIMP type snce plated

Environmental

Solderability Complies with IEC 68-2-20

Temperature range -20 °C to +70 °C