



Deutsche Version

[Home](#)  
[About Us](#)

**Products**

**Audio**

[Video](#)

[Lighting](#)

[Data Connectors](#)

[Industrial](#)

[Support](#)

[News](#)

[Sitemap](#)

Search

PRODUCTS ONLY

Search

© Neutrik® AG  
All rights reserved  
[Legal Notices](#)



Audio

## Phono (RCA)

[back](#)

**NYS373-\***

### Product

Connector Type Jack

Gender female

### Electrical

Contact resistance < 10 mΩ

Dielectric strength 0,5 kVdc

Rated current per contact depends on mated connector A

### Mechanical

Cable O.D. ≤ 6 mm

Insertion force ≤ 20 N

Withdrawal force > 5 N

Lifetime > 1000 mating cycles

Wire size 24 AWG

### Material

Bushing PVC

Contact plating 0.2 μm Au

Contacts Brass (CuZn39Pb3)

Insert Polyamide (PA 6 30 % GR)

Shell Zinc diecast (ZnAl4Cu1) Black

Strain relief Internal plastic chuck

### Environmental

Solderability Complies with IEC 68-2-20

Temperature range -20 °C to +70 °C