

FEATURES

- Door and window switch
- Surface mounting
- Proximity switch activation
- Normally open configuration
- Switching current of 500 (DC) mA
- Switching voltage of 50 V DC
- Operating gap of 15mm
- White-coloured
- Typical contact resistance of 1 Ohm
- Operating distance of 15 mm
- RoHS compliant for restricted hazardous substances
- Depth of 14 mm
- Height of 14 mm
- Width of 60 mm

RS PRO Door and Window Switch Surface Mount 500 (dc)mA, 50V dc

RS Stock No.: 122-0715



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

These RS PRO door and window switches are well-suited for use with both commercial and residential alarm systems to deter intruders away from your home or business. When a window (or door) fitted with the switch is opened, the signal it generates is broken, alerting the alarm system.

A 500 (DC) mA switching current provides a reliable power level that's unlikely to be burnt out. The switches come with a 300 mm-long cable, so you can fit them onto doors and windows without restricting where to install the actual alarm.

General Specifications

Activation Type	Proximity Switch
Colour	White
Switch Configuration	Normally Open
Operating Gap	15mm
Applications	Commercial and Residential, Home or Offices

Electrical Specifications

Switching Current	500 mA (DC)
Switching Voltage	50VDC
Maximum Power	10 W/VA
Contact Resistance	1Ω Typical

Mechanical Specifications

Mounting Type	Surface Mount
Dimensions	14mm x 14mm x 60mm
Depth	14mm
Height	14 mm
Width	60mm

Operation Environment Specifications

Operating Temperature	-10°C to +60°C
------------------------------	----------------

Approvals

Compliance/Certifications	RoHS Compliant, ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007
----------------------------------	---

