






Notes: (Unless Otherwise Specified)

1. Waterproof Rate: IP67.
2. Suitable Cable OD=4.0mm To 6.0 mm.
3. Recommend Cover Torque: 6~7 Kgf-cm.
4. Recommend Gland Nut Torque: 9~10 Kgf-cm.
5. RoHS Compliant.

REV	ECN#	DESCRIPTION OF REVISION	DRAW BY DATE	CHECK BY DATE	APPROVE BY DATE
01			Hank 12/22/15	Lucas 12/22/15	Ray 12/22/15



11	Rubber Pad	Silicone Color: Black	1
10	Holder	Thermoplastic Color: Black	1
9	PCB	FR-4 Color: -	1
8	USB-A Plug	Housing: Thermoplastic, Color: Black Contacts: Copper Alloy, Finish: Au Plated Shell: Copper Alloy, Finish: Ni Plated	1
7	Gland Nut	Thermoplastic Color: Black	1
6	Cage	Thermoplastic Color: White	1
5	Gland	Silicone Color: Green	1
4	Cover	Thermoplastic Color: Black	1
3	D-Ring	Silicone Color: Red	1
2	Screw Nut	Copper Alloy Finish: Ni Plated	1
1	Housing	Thermoplastic Color: Black	1
Item	Part Name	Material / Finish	Qty



Mating Parts:
122-3030
122-3031

TITLE						REV.
USB-A Metal C3 Field Installable Cable End Screw						01
	B	1:1	Hank 12/22/15	Lucas 12/22/15	Ray 12/22/15	X.X ± 0.5 X.XX ± 0.2
THIRD ANGLE PROJECTION	SIZE	SCALE	DRAW / DATE	CHECK / DATE	APPROVE / DATE	X.XXX ± 0.05 ANGLES ± 1°
						mm
						L/1
						TOLERANCES
						UNIT
						SHEET

RS Stock No 122-3029
