



Search within category GO

BSV14X-E



Butt Splice, 16 – 14 AWG, vinyl insulated, convenience package.

BUY NOW

DESIGN / INSTALL

Specs Packaging Details Tools Documents [★ Add to Favorites](#) [Add to BOM](#)

Style	Butt Splice
Wire Range In. (mm ²)	16 - 14 AWG (1.5 - 2.5)
Barrel Configuration	Expanded
Barrel Type	Brazed Seam
Base Material	Copper
Insulation	Vinyl
Panduit Color Code	Blue
Plating Type	Tinned
Part Number Series	BSV
Length In (mm)	1.04 (26.4)
Max. Insulation Diameter In. (mm)	0.211 (5.4)
Wire Strip Length In. (mm)	5/16" (7.9)
Flammability Rating	V0
Max. Voltage Rating	600V
CA-800/EZ Series Crimp Die	—
CA9 Series Crimp Die	—
Tool	CT-100A, CT-600-A, CT-1550, CT-1551, CT-2500
CSA Certified	C22.2 No 65
UL Listed	UL 486C
Packaging Type	Bag
Pieces Per Reel	—
Material	Vinyl
Part Features	<ul style="list-style-type: none"> Expanded wire entry designed to accommodate wire with a larger insulation thickness Designed to splice two solid or stranded wires together to repair or lengthen wires Internal wire stop assures proper length of insertion into terminal barrel
RoHS Compliancy Status	Compliant
Min. Order Qty.	20