



	part. no.		Ø	wire gauge		stripping length	identification	
	silverplated	goldplated		mm <sup>2</sup>	AWG			
male contact	09 33 000 6127	09 33 000 6117	0,90	0,14-0,37	26-22	7,5	no groove	1)
	09 33 000 6121	09 33 000 6122	1,15	0,5	20		no groove	
	09 33 000 6114	09 33 000 6115	1,3	0,75	18		1 groove <1>	
	09 33 000 6105	09 33 000 6118	1,45	1	18		1 groove	
	09 33 000 6104	09 33 000 6116	1,75	1,5	16		2 grooves	
	09 33 000 6102	09 33 000 6123	2,25	2,5	14		3 grooves	
	09 33 000 6106		2,55	3	12		1 wide groove	
	09 33 000 6107	09 33 000 6119	2,85	4	12		no groove	
female contact	09 33 000 6227	09 33 000 6217	0,90	0,14-0,37	26-22	7,5	no groove	1)
	09 33 000 6220	09 33 000 6222	1,15	0,5	20		no groove	
	09 33 000 6214	09 33 000 6215	1,3	0,75	18		1 groove <1>	
	09 33 000 6205	09 33 000 6218	1,45	1	18		1 groove	
	09 33 000 6204	09 33 000 6216	1,75	1,5	16		2 grooves	
	09 33 000 6202	09 33 000 6223	2,25	2,5	14		3 grooves	
	09 33 000 6206		2,55	3	12		1 wide groove	
	09 33 000 6207	09 33 000 6221	2,85	4	12		no groove	

1) only for Buchanan crimping tool adjusting Ø1,0

		All Dimensions in mm Original Size DIN A4		Scale 2:1	Free size tol.		Ref.		
		All rights reserved Department EL PD - DE		Created by SCHULZI	Inspected by MOOR	Standardisation TIEMANNA	Date 2014-10-23	State Final Release	
		HARTING Electric GmbH & Co. KG		Title Han E contacts male/female				Doc-Key / ECM-Nr. 100089025/UGD/005/A 500000081115	
part. no.		D-32339 Espelkamp		Type TB	Number 09 33 000 6XXX			Rev. A	Page 1/1